

9930 Series


Recessed Asymmetric Exam Light
Halogen Incandescent

Project

Type

Project Location

Catalog #



Quartz lamp produces true color rendition.

Recessed ceiling installation keeps light out of patient's direct field of vision.

Provides for staff and patient comfort without sacrificing efficiency.

The 250 watt quartz examination light recesses in the ceiling at the head of the bed. An angled aperture and optical lens minimize glare for the patient while providing illumination for an exam.


Unit is generally used with a wall mounted timer to prevent heat buildup and extend lamp life. Patient and staff can be free of troublesome hand held examination lights.



Ellipsoidal reflector



Optional Timer



Fresnel focusing lens



9930 Series

Recessed Asymmetric Exam Light
Halogen Incandescent

Project

Type

CROSS SECTION (9930 Illustrated)



SPECIFICATIONS

CONSTRUCTION

20 gauge cold rolled steel. Inner door frame has full length piano hinge. Captive thumb screw secures frame.

ELECTRICAL

Mini-Cand 250 watt quartz porcelain socket. 120 volt only.

LENS

Heat resistant fresnel focusing lens.

REFLECTOR

Ellipsoidal aluminum reflector with high reflectance factor finish.

FINISH

Bonderized matte black baked enamel aperture recess. Bonderized white baked enamel housing.

INSTALLATION

7/8" diameter knockouts for electrical connection. Optional plaster frame and hanger assembly. Not recommended for installation near air conditioning vents.

LABELS

UL & I.B.E.W.

LAMPS

One Q250 CL/MC quartz T-4 (lamps not included).

Note: Fixture is rated for use with 150° C supply wire. For connection to remote outlet box with 90° C wiring, an optional 4' flexible conduit "whip" can be specified.

ORDERING INFORMATION

Catalog No.	Description	L	W	D
9930	250W Quartz Examination Light	12"	12"	9 1/2"

OPTIONAL EQUIPMENT

/PFH9930	Plaster Frame & Hangers
TIMER	Wall Mounted 1-15 Minute Timer



© 2013 Koninklijke Philips N.V. (Royal Philips). All rights reserved.
Specifications are subject to change without notice.
www.philips.com/luminaires

E4-0 06/13 page 2 of 2

Philips Lighting Company
200 Franklin Square Drive
Somerset, NJ 08873
Phone: 855-486-2216

Philips Lighting Company
281 Hillmount Road
Markham ON, Canada L6C 2S3
Phone: 800-668-9008